

Multi-pin node VABE-S6-LT-C-S10-R5

Part number: 549047

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Max. no. of valve positions	10 for double-solenoid valves 20 for single-solenoid valves
Max. residual current	10 A
Nominal operating voltage DC	24 V
Permissible voltage fluctuations	+/- 10%
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Ambient temperature	-5 °C ... 50 °C
Product weight	790 g
Number of electrical connections	10
Electrical actuation	Multi-pin
Electrical connection	5-pin M12 Plug
Cover material	PA
Housing material	Die-cast aluminum