

# Solenoid coil MD-2-24VDC-PA

Part number: 549903

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Duty cycle	100%
Coil characteristics	24 V DC: 6.8 W
Permissible voltage fluctuations	+/- 10%
LABS (PWIS) conformity	VDMA24364-B2-L
Degree of protection	IP65
Ambient temperature	-20 °C ... 50 °C
Max. tightening torque of pneumatic fitting	0.5 Nm
Product weight	110 g
Electrical connection	As per DIN EN 175301-803
Type of mounting	With knurled nut
Note on materials	RoHS compliant
Solenoid coil material	Duroplast Copper Steel
Material of winding	Copper