

# Solenoid coil MH-2-110VAC-PA

Part number: 549907

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
Switching position indication	no
Min. pick-up time	12 ms
Duty cycle	100%
Power factor cos {phi}	0.7
Coil characteristics	110 V AC: 14.0 VA
Permissible frequency fluctuations	+/- 10%
Permissible voltage fluctuations	+/- 10 %
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
LABS (PWIS) conformity	VDMA24364 zone III
Degree of protection	IP65
Note on degree of protection	IP00 without connector socket
Ambient temperature	-20 °C ... 50 °C
Max. tightening torque of pneumatic fitting	2 Nm
Product weight	150 g
Electrical connection	as per DIN EN 175301-803
Type of mounting	With lock nut
Solenoid coil material	Duroplast Copper Steel
Material of winding	Copper