

Plug socket with cable KMYZ-4-5,0-B-EX

Part number: 550482

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Maritime classification | See certificate |
| Type of mounting | On air solenoid valve with M2 central screw |
| Mounting position | Any |
| Product weight | 62.5 g |
| Electrical connection | Socket, angled Cable Rectangular design MSZB |
| DC operating voltage range | 3 V ... 36 V |
| Nominal operating voltage DC | 24 V |
| Current rating at 40° C | 1 A |
| Surge resistance | 0.9 kV |
| Protective earth connection | Not available |
| Cable length | 5 m |
| Cable characteristic | Standard |
| Cable design | 2 x 0.35 mm ² |
| Degree of protection | IP40 |
| Ambient temperature | -10 °C ... 50 °C |
| CE marking (see declaration of conformity) | As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Note on materials | RoHS-compliant |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| Material of cable sheath | PVC |
| Housing material | PA |
| Material of pin contacts | Bronze |