

# Coupling EAMC-30-35-6.35-12

Part number: 550995

FESTO



 [General operating condition](#)

## Data sheet

| Feature                | Value                 |
|------------------------|-----------------------|
| Diameter of holder 1   | 6.35 mm               |
| Diameter of holder 2   | 12 mm                 |
| Size                   | 30                    |
| Nominal length         | 35 mm                 |
| Mounting position      | Any                   |
| Max. rotational speed  | 8000 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L        |
| Storage temperature    | -25 °C ... 60 °C      |
| Relative air humidity  | 0 - 95 %              |
| Ambient temperature    | -25 °C ... 60 °C      |
| Mass moment of inertia | 6.1 kgmm <sup>2</sup> |
| Transferable torque    | 7.5 Nm                |
| Product weight         | 45 g                  |
| Note on materials      | RoHS-compliant        |