

Coupling EAMC-30-32-6-6.35

Part number: 551002

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 1	6 mm
Diameter of holder 2	6.35 mm
Size	30
Nominal length	32 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	5.87 kgmm ²
Transferable torque	6.5 Nm
Product weight	48 g
Note on materials	RoHS-compliant