

Coupling EAMC-30-32-8-11

Part number: 551004

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|------------------------|------------------------|
| Diameter of holder 1 | 8 mm |
| Diameter of holder 2 | 11 mm |
| Size | 30 |
| Nominal length | 32 mm |
| Mounting position | Any |
| Max. rotational speed | 8000 rpm |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95 % |
| Ambient temperature | -25 °C ... 60 °C |
| Mass moment of inertia | 5.87 kgmm ² |
| Transferable torque | 12.5 Nm |
| Product weight | 48 g |
| Note on materials | RoHS-compliant |