

# Plastic tubing PEN-10X1,5-RT

Part number: 551477

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	40 mm
Inside diameter	7 mm
Min. bending radius	23.5 mm
Tubing characteristics	Suitable for energy chains
Temperature-dependent operating pressure	-0.095 MPa ... 1 MPa
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Temperature-dependent operating pressure	-13.775 psi ... 145 psi
Information on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Certification	TÜV
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
Ambient temperature	-30 °C ... 60 °C
Product weight by length	0.03766 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Red
Shore hardness	D 52 +/-3
Note on materials	RoHS compliant
Material of pneumatic tubing	Protective grounding