


Pneumatic muffler UOS-1

Part number: 552252

FESTO



[PDF](#) [General operating condition](#)

Data sheet

Feature	Value
Type of seal on screwed plug	without seal
Mounting position	Any
Structural design	Muffler open
Symbol	00992064
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [:-:-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Noise level	75 dB(A)
Ambient temperature	-10 °C ... 50 °C
Type of mounting	With external thread
Product weight	200 g
Pneumatic connection	G1
Cushioning insert material	Protective grounding
Note on materials	RoHS compliant
Housing material	POM
Sleeve material	Wrought aluminum alloy