

Fiber-optic cable SOOC-DS-C-M4-2-R15

Part number: 552842

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Note on materials	RoHS-compliant
Method of measurement	Reflection light sensor
Minimum object diameter	0.1 mm
Special feature of fibre-optic cable	Coaxial
Working range	75 mm
Ambient temperature	-55 °C ... 70 °C
Head size	M4
Fibre-optic cable length	2 m
Min. bending radius	15 mm
Max. tightening torque	2 Nm
Outside diameter	1.25 mm
Housing material	Brass, nickel-plated
Fiber-optic cable	PE
Degree of protection	IP66
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III