

Manifold rail MHJ9-PN16

Part number: 553123

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|--|
| Width dimension | 10 mm |
| Max. no. of valve positions | 16 Versions according to customer specifications possible |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Product weight | 390 g |
| Type of mounting | With mounting bracket |
| Pneumatic connection 1 | G3/8 |
| Pneumatic connection 2 | Not ducted |
| Note on materials | RoHS-compliant |
| Manifold rail material | Wrought aluminum alloy, anodized |