

Manifold rail MHJ9-PN16

Part number: 553123

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Width dimension	10 mm
Max. no. of valve positions	16 Versions according to customer specifications possible
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Product weight	390 g
Type of mounting	With retaining bracket
Pneumatic connection 1	G3/8
Pneumatic connection 2	Not ducted
Note on materials	RoHS compliant
Manifold rail material	Wrought aluminum alloy, anodized