

Vacuum filter VAF-DB-1/2

Part number: 553141

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Vertical
Grade of filtration	80 µm
Symbol	00991483
Operating pressure	-0.95 bar ... 0 bar
Information on operating pressure	Only for use in open vacuum systems
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity	VDMA24364 Zone III
Ambient temperature	-5 °C ... 50 °C
Max. tightening torque	20.5 Nm
Product weight	162 g
Type of mounting	With wall/surface bracket
Pneumatic connection	G1/2
Vacuum connection	G1/2
Note on materials	RoHS compliant
Seals material	NBR
Compressed air filter material	Protective grounding
Housing material	Reinforced PP
Material of bowl	PA
Ejector pulse suitability	≤7 bar