

Bellows kit DADB-V6-32-S10-50

Part number: 553271

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---|
| Outside diameter | 38 mm |
| Size | 32 |
| Stroke range | 10 mm ... 50 mm |
| Piston rod extension | 29 mm |
| Design | Round |
| Mounting position | Any |
| Structural design | With ducted exhaust |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Media resistance | Dust Chips Oils Grease Petrol |
| Degree of protection | IP54 |
| Ambient temperature | -10 °C ... 80 °C |
| Product weight | 29 g |
| Type of mounting | Push-fitted With threaded pin |
| Pneumatic connection | G1/8 |
| Note on materials | RoHS compliant |
| Adaption parts material | PA-reinforced |
| Seals material | NBR |
| Bellows material | NBR |
| Threaded pin material | high-alloy stainless steel |