

# Bellows kit DADB-V6-100-S10-50

Part number: 553371

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Outside diameter	93 mm
Size	100
Stroke range	10 mm ... 50 mm
Piston rod extension	25 mm
Design	Round
Mounting position	Any
Structural design	With ducted exhaust
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Media resistance	Dust Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C ... 80 °C
Product weight	124 g
Type of mounting	Push-fitted With threaded pin
Pneumatic connection	G1/4
Note on materials	RoHS compliant
Adaption parts material	PA-reinforced
Seals material	NBR
Bellows material	NBR
Threaded pin material	high-alloy stainless steel