

Bellows kit DADB-S1-40-S476-500

Part number: 553479

FESTO



 General operating condition

Data sheet

Feature	Value
Outside diameter	46 mm
Size	40
Stroke range	476 mm ... 500 mm
Piston rod extension	132 mm
Design	Round
Mounting position	Any
Structural design	with ducted exhaust air
Corrosion resistance class (CRC)	3 - High corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Metals with more than 5% by mass of copper, zinc or nickel are excluded from use. The exceptions are nickel in steel, chemically nickel-plated surfaces, printed circuit boards, cables, electrical plug connectors and coils.
Media resistance	Stäube Chips Oils Grease Petrol
Degree of protection	IP54
Ambient temperature	-10 °C ... 80 °C
Product weight	137 g
Type of mounting	With threaded pin With internal thread
Pneumatic connection	G1/8
Note on materials	RoHS-compliant
Adaption parts material	PA-reinforced
Seals material	NBR
Bellows material	NBR
Threaded pin material	High-alloy stainless steel