

Mounting SAMH-G3-Q

Part number: 553569

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Design	For dovetail slot
Ambient temperature	-10 °C ... 60 °C
Type of mounting	With through-hole
Max. tightening torque	3 Nm
Product weight	10 g
Housing material	Wrought aluminum alloy
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L