

Clevis foot LSN-50

Part number: 5563

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	50
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C ... 120 °C
Max. load capacity	2.5 kN
Product weight	366 g
Note on materials	RoHS-compliant
Mounting material	High-alloy steel
Bushing material	Wrought aluminum alloy
Rod end bearing material	Steel PTFE