

Clevis foot LSN-80

Part number: 5565

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|-------------------------------|
| Size | 80 |
| Corrosion resistance class (CRC) | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -40 °C ... 120 °C |
| Max. load capacity | 6 kN |
| Product weight | 755 g |
| Note on materials | RoHS compliant |
| Mounting material | Spheroidal graphite cast iron |
| Bushing material | Wrought aluminum alloy |
| Rod end bearing material | Steel PTFE |