

Coupling EAMC-30-35-8-9

Part number: 557390

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 1	8 mm
Diameter of holder 2	9 mm
Size	30
Nominal length	35 mm
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	6.1 kgmm ²
Transferable torque	8.2 Nm
Product weight	45 g
Note on materials	RoHS-compliant