

# Manifold rail VABM-C8-12E-G14-20-M1

Part number: 557669

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                   | Value                   |
|---|-------------------------|
| Width dimension                           | 12 mm                   |
| Max. no. of valve positions               | 20                      |
| Corrosion resistance class (CRC)          | 0 - No corrosion stress |
| LABS (PWIS) conformity                    | VDMA24364-B1/B2-L       |
| Max. tightening torque for valve mounting | 0.6 Nm                  |
| Max. tightening torque for wall mounting  | 5 Nm                    |
| Product weight                            | 1296 g                  |
| Pneumatic connection 1                    | G1/4                    |
| Pneumatic connection 3                    | G1/4                    |
| Pneumatic connection 5                    | G1/4                    |
| Note on materials                         | RoHS-compliant          |
| Manifold rail material                    | Wrought aluminum alloy  |