


Axial kit EAMM-A-K48-60G

Part number: 557986

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Max. rotational speed	8000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	14.5 kgmm ²
Transferable torque	12.5 Nm
Product weight	300 g
Interface code, actuator	K48
Interface code, motor in	60G
Note on materials	RoHS-compliant