

# Coupling EAMD-19-15-9-8X10

Part number: 557999

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Diameter of holder 1	9 mm
Diameter of holder 2	8 mm
Size	19
Nominal length	15 mm
Mounting position	Any
Max. rotational speed	10000 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	0.445 kgmm <sup>2</sup>
Transferable torque	2 Nm
Product weight	13.5 g
Note on materials	RoHS-compliant