

Coupling EAMD-67-51-24-32X32-U

Part number: 558008

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 1	24 mm
Diameter of holder 2	32 mm
Size	67
Nominal length	51 mm
Mounting position	Any
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	374 kgmm ²
Transferable torque	143 Nm
Product weight	736 g
Note on materials	RoHS-compliant