

Drive shaft adapter EAMB-34-6-25X26-23X27

Part number: 558037

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 1	25 mm
Diameter of holder 2	23 mm
Size	120
Nominal length	26 mm
Mounting position	Any
Max. rotational speed	5500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	18.2 kgmm ²
Transferable torque	100 Nm
Product weight	201 g
Note on materials	RoHS compliant