

Drive shaft adapter EAMB-44-7-35X30-32X32

Part number: 558038

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Diameter of holder 1	35 mm
Diameter of holder 2	32 mm
Size	185
Nominal length	30 mm
Mounting position	Any
Max. rotational speed	4500 rpm
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	75.3 kgmm ²
Transferable torque	200 Nm
Product weight	463 g
Note on materials	RoHS compliant