

Plastic tubing PLN-10X1,5-SI

Part number: 558214

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Outside diameter	10 mm
Bending radius relevant for flow rate	57 mm
Inside diameter	7 mm
Min. bending radius	22 mm
Temperature-dependent operating pressure	-0.095 MPa ... 1.4 MPa
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Temperature-dependent operating pressure	-13.775 psi ... 203 psi
Information on operating pressure	Water: max. 0.6 MPa at 0 - 50 °C
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
LABS (PWIS) conformity	VDMA24364-B2-L
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
For use in the food industry	See supplementary material information
Ambient temperature	-30 °C ... 80 °C
Product weight by length	0.0375 kg/m
Pneumatic connection	For plug connection outside diameter 10 mm
Color	Silver
Note on materials	RoHS-compliant
Material of pneumatic tubing	PE