

# Plastic tubing PUN-H-6X1-SI

Part number: 558279

FESTO



 General operating condition

## Data sheet

Feature	Value
Outside diameter	6 mm
Bending radius relevant for flow rate	26 mm
Inside diameter	4 mm
Min. bending radius	10 mm
Application note	TPE-U Ether based
Tubing characteristics	Suitable for energy chains
Operating pressure for entire temperature range	-0.095 MPa ... 0.6 MPa
Operating pressure for entire temperature range	-0.95 bar ... 6 bar
Operating pressure for entire temperature range	-13.775 psi ... 87 psi
Temperature-dependent operating pressure	-0.095 MPa ... 1 MPa
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Temperature-dependent operating pressure	-13.775 psi ... 145 psi
Information on operating pressure	Water: temperature-dependent operating pressure, see diagram, max. 0.3 MPa at 0 - 60 °C
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0527 00
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-] Water (liquid, ice-free)
Material fire test	UL94 HB
LABS (PWIS) conformity	VDMA24364-B2-L
Suitability for the production of Li-ion batteries	Suitable for battery production with reduced Cu/Zn/Ni values (F1a)
Cleanroom suitability, measured according to ISO 14644-14	Statically installed element, no meaningful evaluation possible according to ISO 14644-1
For use in the food industry	See supplementary material information
Ambient temperature	-35 °C ... 60 °C
Product weight by length	0.0183 kg/m
Pneumatic connection	For plug connection outside diameter 6 mm For barbed fitting, inside diameter 4 mm, with union nut
Color	Silver
Shore hardness	D 52 +/-3
Note on materials	RoHS-compliant
Material of pneumatic tubing	TPE-U(PU)