

Push-in L-fitting NPQM-LH-G18-Q8-P10

Part number: 558831

FESTO



 General operating condition

Data sheet

Feature	Value
Size	Standard
Nominal width	6.5 mm
Type of seal on screwed plug	Sealing ring
Design	L-shape
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.095 MPa ... 1.6 MPa
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating pressure for entire temperature range	-13.775 psi ... 232 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Lubricated operation possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-20 °C ... 70 °C
Nominal tightening torque	6 Nm
Tolerance for nominal tightening torque	±20%
Product weight	30.5 g
Type of mounting	Hollow bolt with external hex
Pneumatic connection 1	External thread G1/8
Pneumatic connection 2	for pneumatic tubing outside diameter 8 mm
Releasing ring color	Silver
Note on materials	RoHS compliant
Housing material	Brass, nickel-plated
Hollow bolt material	Brass, nickel-plated
Material of tubing seal	NBR