

Connecting cable VMPAL-KM-V-SD44-IP67-2,5

Part number: 560422

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Product weight	462 g
Electrical connection	Cable with plug
Cable length	2.5 m
Cable characteristic	Standard
Min. cable bending radius	115 mm
Cable diameter	9.6 mm
Cable design	36 x 0.25 mm ²
Degree of protection	IP67 As per IEC 60529
Ambient temperature with flexible cable installation	-5 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	PVC