

Connecting cable VMPAL-KM-V-SD44-IP67-2,5

Part number: 560422

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|-------------------------------|
| Product weight | 462 g |
| Electrical connection | Cable with plug |
| Cable length | 2.5 m |
| Cable characteristic | Standard |
| Min. cable bending radius | 115 mm |
| Cable diameter | 9.6 mm |
| Cable design | 36 x 0.25 mm ² |
| Degree of protection | IP67 as per IEC 60529 |
| Ambient temperature with flexible cable installation | -5 °C ... 80 °C |
| CE marking (see declaration of conformity) | As per EU RoHS directive |
| UKCA marking (see declaration of conformity) | To UK RoHS instructions |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Note on materials | RoHS-compliant |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Material of cable sheath | PVC |