

Hood VMPAL-KM-SD25-IP67-0

Part number: 560428

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Product weight	100 g
Electrical connection	Customizable assembly
Approved cable diameter	5 mm ... 13 mm
Connection cross section	0.2 mm ² ... 0.5 mm ²
Degree of protection	IP67 As per IEC 60529
Ambient temperature	-5 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress