

# Axial kit EAMM-A-K38-57A

Part number: 560681

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	3.6 Nm
Product weight	130 g
Interface code, actuator	K38
Interface code, motor in	57A
Note on materials	RoHS-compliant