

# Motor flange EAMF-A-38A-57A

Part number: 560692

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value            |
|----------------------------------|------------------|
| Mounting position                | Any              |
| LABS (PWIS) conformity           | VDMA24364-B2-L   |
| Storage temperature              | -25 °C ... 60 °C |
| Relative air humidity            | 0 - 95 %         |
| Ambient temperature              | -10 °C ... 60 °C |
| Product weight                   | 79 g             |
| Interface code, motor in         | 57A              |
| Interface code, coupling housing | 38A              |
| Note on materials                | RoHS-compliant   |