

# Motor flange EAMF-A-38A-57A

Part number: 560692

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Mounting position	Any
LABS (PWIS) conformity	VDMA24364-B2-L
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95%
Ambient temperature	-10 °C ... 60 °C
Product weight	79 g
Interface code, motor in	57A
Interface code, coupling housing	38A
Note on materials	RoHS compliant