


Regulator plate VABF-S4-1-R5C2-C-10E

Part number: 560772

FESTO



[PDF General operating condition](#)

Data sheet

Feature	Value
Width	26 mm
Based on norm	ISO 15407-2
Mounting position	Any
Controller function	Constant output pressure With secondary exhausting
Symbol	00991862
Optional pressure gauge	Possible
Operating pressure	1 MPa
Operating pressure	10 bar
Pressure regulation range MPa	0.05 MPa ... 0.85 MPa
Pressure regulation range	0.5 bar ... 8.5 bar
Pressure regulation range psi	7.25 psi ... 123.25 psi
Inlet pressure 1	0.5 bar ... 10 bar
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Degree of protection	IP65 NEMA 4
Pilot medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Ambient temperature	-5 °C ... 50 °C
Product weight	735 g
Vertical stacking mounting type	On manifold sub-base On individual sub-base
Pressure gauge connection	With retaining clamp
Material of operator panel	PA
Controller housing material	Die-cast aluminum