


# End plate VABE-S6-2RZ-N34

Part number: 560840

FESTO



 [General operating condition](#)

## Data sheet

Feature	Value
Based on norm	ISO 5599-2
Mounting position	Any
Valve terminal type	44
Operating pressure	-0.09 MPa ... 1 MPa
Operating pressure	-0.9 bar ... 10 bar
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Product weight	336 g
Pilot air port 12	1/4 NPT
Pilot air port 14	1/4 NPT
Pneumatic connection 1	3/4 NPT
Pneumatic connection 3	3/4 NPT
Pneumatic connection 5	3/4 NPT
Note on materials	RoHS compliant
End plate material	Die-cast aluminum