

Plate VMPAL-EG-QS10

Part number: 560957

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|---|
| Width | 20.5 mm |
| Length | 107.3 mm |
| Integrated function | Ducted exhaust air |
| Valve manifold design | Valve sizes can be mixed |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Pressure regulation range | 0.5 bar ... 5 bar |
| Inlet pressure 1 | 0.5 bar ... 10 bar |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 30 g |
| Pneumatic port 3/5 combined | For pneumatic tubing outside diameter 10 mm |
| Note on materials | RoHS-compliant |
| Plate material | PA |