

Sub-base VMPAL-AP-10-QS4-2-T1

Part number: 561018

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|--|
| Width | 10.7 mm |
| Length | 107.3 mm |
| Width dimension | 10.7 mm |
| Valve size | 10 mm |
| Pressure zone separation | Channel 1 |
| Max. no. of valve positions | 1 |
| Flow direction | Reversible |
| Valve manifold design | Valve sizes can be mixed |
| Max. no. of solenoid coils | 2 |
| Operating pressure | -0.09 MPa ... 1 MPa |
| Operating pressure | -0.9 bar ... 10 bar |
| Pilot pressure MPa | 0.3 MPa ... 0.8 MPa |
| Pilot pressure | 3 bar ... 8 bar |
| Operating medium | Compressed air as per ISO 8573-1:2010 [7:4:4] |
| Information on operating and pilot media | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC) | 3 - High corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| Ambient temperature | -5 °C ... 50 °C |
| Product weight | 30 g |
| Pneumatic connection 2 | for pneumatic tubing outside diameter 4 mm |
| Pneumatic connection 4 | for 4 mm tubing O.D. |
| Note on materials | RoHS-compliant |
| Material of sub-base | PA-reinforced |