

Blanking plug QSPC10

Part number: 562243

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Size	Standard
Design	Straight design
Pack size	10
Operating pressure for entire temperature range	0 MPa ... 0.8 MPa
Operating pressure for entire temperature range	0 bar ... 8 bar
Operating pressure for entire temperature range	0 psi ... 116 psi
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	0 - No corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-5 °C ... 60 °C
Product weight	0.4 g
Type of mounting	Mounting pin
Pneumatic connection 1	Cartridge 10 mm
Note on materials	RoHS-compliant
Blanking plug material	POM
O-ring material	NBR