

# Connecting cable VMPAL-KM-V-SD25-IP67-

Part number: 562389

FESTO



 [General operating condition](#)

## Data sheet

Overall data sheet – Individual values depend upon your configuration.

Feature	Value
Electrical connection	Cable with plug
Cable characteristic	Standard
Min. cable bending radius	84 mm
Cable diameter	11.2 mm
Cable design	25 x 0.34 mm <sup>2</sup>
Degree of protection	IP67 as per IEC 60529
Ambient temperature with flexible cable installation	-5 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	PVC