

Connecting cable NEBV-M8W4L-E-10-M8G3

Part number: 562470

FESTO



 General operating condition

Data sheet

Feature	Value
Conforms to standard	ISO 20401
Switching status indication	LED yellow
Product weight	170 g
Electrical connection	4-pin/3-pin Angled socket/straight plug M8x1/M8x1
DC operating voltage range	20.4 V ... 26.4 V
Current rating at 40° C	3 A
Cable length	10 m
Cable characteristic	Suitable for energy chains
Min. cable bending radius	35 mm
Cable diameter	3.3 mm
Cable design	2 x 0.25 mm ²
Degree of protection	IP65 IP67
Ambient temperature	-10 °C ... 50 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Material of cable sheath	TPE-U(PUR)
Housing material	TPE-U(PU)
Material of pin contacts	Brass Gold-plated
Insulating sheath material	PVC