

Motor flange EAMF-A-28D-28M

Part number: 562664

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|------------------|
| Mounting position | Any |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 18 g |
| Interface code, motor in | 28M |
| Interface code, coupling housing | 28D |
| Note on materials | RoHS compliant |