


Motor flange EAMF-A-38A-40A

Part number: 562667

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|----------------------------------|------------------|
| Mounting position | Any |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Storage temperature | -25 °C ... 60 °C |
| Relative air humidity | 0 - 95% |
| Ambient temperature | -10 °C ... 60 °C |
| Product weight | 47 g |
| Interface code, motor in | 40A |
| Interface code, coupling housing | 38A.2 |
| Note on materials | RoHS compliant |