

# Coupling EAMC-16-20-4-8

Part number: 562675

FESTO



 [General operating condition](#)

## Data sheet

| Feature                | Value                  |
|------------------------|------------------------|
| Diameter of holder 1   | 4 mm                   |
| Diameter of holder 2   | 8 mm                   |
| Size                   | 16                     |
| Nominal length         | 20 mm                  |
| Mounting position      | Any                    |
| Max. rotational speed  | 10000 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L         |
| Storage temperature    | -25 °C ... 60 °C       |
| Relative air humidity  | 0 - 95 %               |
| Ambient temperature    | -25 °C ... 60 °C       |
| Mass moment of inertia | 0.28 kgmm <sup>2</sup> |
| Transferable torque    | 0.7 Nm                 |
| Product weight         | 8 g                    |
| Note on materials      | RoHS-compliant         |