

# Solenoid coil VACC-S13-18-A1-2U

Part number: 562891

FESTO



 [General operating condition](#)

## Data sheet

| Feature                                      | Value   |
|--|---|
| Actuation type                               | Electrical  |
| Mounting position                            | Any   |
| Switching position indication                | no  |
| Duty cycle                                   | 100%  |
| Insulation class                             | H   |
| Coil characteristics                         | 110 V DC: 1.8 W<br>110 V AC: 50/60 Hz, power 1.8 VA |
| Permissible voltage fluctuations             | -15 % / +10 %                                       |
| CE marking (see declaration of conformity)   | As per EU low voltage directive                     |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment         |
| Corrosion resistance class (CRC)             | 4 - Particularly high corrosion stress              |
| LABS (PWIS) conformity                       | VDMA24364 zone III                                  |
| Degree of protection                         | IP65  |
| Ambient temperature                          | -20 °C ... 60 °C                                    |
| Product weight                               | 210 g   |
| Electrical connection                        | Form A<br>Plug<br>as per EN 175301-803              |
| Note on materials                            | RoHS-compliant                                      |
| Solenoid coil material                       | PA<br>UP  |