

Solenoid coil VACC-S13-18-A1-2U

Part number: 562891

FESTO



 [General operating condition](#)

Data sheet

| Feature | Value |
|--|---|
| Actuation type | Electrical |
| Mounting position | Any |
| Switching position indication | No |
| Duty cycle | 100% |
| Insulation class | H |
| Coil characteristics | 110 V DC: 1.8 W 110 V AC: 50/60 Hz, power 1.8 VA |
| Permissible voltage fluctuations | -15% / +10% |
| CE marking (see declaration of conformity) | As per EU low voltage directive |
| UKCA marking (see declaration of conformity) | To UK instructions for electrical equipment |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| LABS (PWIS) conformity | VDMA24364 Zone III |
| Degree of protection | IP65 |
| Ambient temperature | -20 °C ... 60 °C |
| Product weight | 210 g |
| Electrical connection | Type A Plug As per EN 175301-803 |
| Note on materials | RoHS compliant |
| Solenoid coil material | PA UP |