

# Solenoid coil VACC-S18-35-A1-1A

Part number: 562907

FESTO



 [General operating condition](#)

## Data sheet

| Feature                          | Value                                  |
|----------------------------------|--|
| Actuation type                   | Electrical                             |
| Mounting position                | Any                                    |
| Switching position indication    | No                                     |
| Duty cycle                       | 100%                                   |
| Insulation class                 | H                                      |
| Coil characteristics             | 24 V AC: 50/60 Hz, power 3.5 VA        |
| Permissible voltage fluctuations | -15% / +10%                            |
| Corrosion resistance class (CRC) | 4 - Particularly high corrosion stress |
| LABS (PWIS) conformity           | VDMA24364 Zone III                     |
| Degree of protection             | IP65                                   |
| Ambient temperature              | -20 °C ... 60 °C                       |
| Product weight                   | 530 g                                  |
| Electrical connection            | Type A<br>Plug<br>As per EN 175301-803 |
| Note on materials                | RoHS compliant                         |
| Solenoid coil material           | PA<br>Steel                            |