

Solenoid coil VACC-S18-35-A1-3A

Part number: 562909

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Actuation type	Electrical
Mounting position	Any
Switching position indication	No
Duty cycle	100%
Insulation class	H
Coil characteristics	230 V AC: 50/60 Hz, power 3.5 VA
Permissible voltage fluctuations	-15% / +10%
CE marking (see declaration of conformity)	As per EU low voltage directive
UKCA marking (see declaration of conformity)	To UK instructions for electrical equipment
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Degree of protection	IP65
Ambient temperature	-20 °C ... 60 °C
Product weight	580 g
Electrical connection	Type A Plug As per EN 175301-803
Note on materials	RoHS compliant
Solenoid coil material	PA Steel