

Sub-base VABS-S7-S-G14-VDE1

Part number: 563396

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Mounting position	Any
Operating pressure	0 MPa ... 1 MPa
Operating pressure	0 bar ... 10 bar
Explosion prevention and protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
LABS (PWIS) conformity	VDMA24364 Zone III
Degree of protection	IP65
Type of mounting	With through-hole
Pneumatic connection 1	G1/4
Pneumatic connection 2	VDI/VDE 3845 (NAMUR)
Pneumatic connection 3	G1/4
Note on materials	RoHS compliant
Seals material	NBR
Plate material	Aluminum, ematal coated